




YGIBS286752N Structural Steel Compression Grounding Connector

By Burndy
Catalog # YGIBS286752N



GROUNDLINK™ Connector for Structural Steel Angled or Parallel Beam; Accommodates: #2 - 4/0 AWG; 3" Length; I-Beam Flange Thickness: 0.613" - 0.675".

Application

For Direct Burial Cables

General

Catalog Number	YGIBS286752N
Connector Type	Tap
EU RoHS Indicator	Yes
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, GROUNDLINK
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039342
UPC 12 Digit	7818100393422

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - I Beam Thickness Range inch	0.563;0.600;0.625;0.575
Dimension - I Beam Thickness inch	0.613" - 0.675"
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2376

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YGIBS283382N_LineArt](#)
[Sales Drawings - SD208416-04_B](#)
[Specifications - YGIBS286752N](#)