



Compression Terminal

By Burndy
Catalog # [YAZ29TC3845](#)

250 kcmil CU, One Hole, 3/8 Stud Size, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.



Application

Wire Termination

General

Color Code	Yellow
Connector Type	LONG BARREL
Die Index	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810240168
UPC 12 Digit	7818102401688

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.4 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Height inch	2.09 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	69 mm
Dimension - Length Overall inch	2.72 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 KCMIL
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - SE..212356-21](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAZ29TC3845-SPEC-EN | REV 8/2023