



YGL29C29TN Compression Cross Grid Connector

By Burndy
Catalog # YGL29C29TN



Cu Compression Ground Connector, Cable to Cable/ Cable to Rebar, # 2 Str. - 250 Kcmil, 1/2"- 5/8" Rod,#3- #4 Rebar (Run), # 2 Str. - 250 Kcmil (Tap), Tin Plated.

General

Connector Type	Tap
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYGRID™
Type	Taps
UPC	781810110850
UPC 12 Digit	7818101108500

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.50 in
Dimension - L Length Overall mm	64 mm
Dimension - Length BB inch	0.75 in
Dimension - Length Overall inch	2.50 in
Dimension - Pad Width inch	1.66 in

Conductor Related

Conductor - Copper Str Size A	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor - Copper Str Size B	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size B Range	2 AWG-250 kcmil
Conductor - Rebar Size A	3 ;4
Conductor - Rebar Size A Range	3 -4
Conductor - Rod Size A	1/2 in;5/8 in
Conductor - Rod Size A Range	1/2 in-5/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size A • CU C Str-Size A • Rod-Size A • Rebar-Size A • CU C Solid-Size B • CU C Str-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd082258-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGL29C29TN-SPEC-EN | REV 8/2023