



YHSA10K6, Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K6](#)

Heat Shrink Ring Terminal For 12 - 10 AWG.



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

General

Catalog Number	YHSA10K6
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524664
UPC 12 Digit	7818105246644

Dimensions

Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.34 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.17 in

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K6_LineArt](#)
[Sales Drawings - 50094158](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YHSA10K6-SPEC-EN | REV 8/2024