



Heat Shrink Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K8BF](#)



Heat Shrink Block Fork Terminal For 16 - 14 AWG.

Application

For Use On Copper Conductor

General

Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Block Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524824
UPC 12 Digit	7818105248244

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.20 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.30 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K6BF_LineArt](#)
[Sales Drawings - 50094184](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YHSA14K8BF-SPEC-EN | REV 5/2024