



YCA28RL2N, Al compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 4/0

By Burndy
Catalog # YCA28RL2N



Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus, Die index: 654.

Application

Aluminum compression HYLUGs for terminating overhead conductors to switch pads and substation or switch yard apparatus.

General

Connector Type	Terminal
Construction Material - Main	Aluminum
Die Index	654
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YCA-RL-2N
UPC	781810810484
UPC 12 Digit	7818108104844

Dimensions

Dimension - B Length inch	2.48 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	168 mm
Dimension - Length Overall inch	6.62 in
Dimension - Outside Diameter inch	1.02 in
Dimension - Pad Width inch	1.40 in

Conductor Related

Conductor - ACSR Cmppt Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AAC

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5550

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCA_LineArt](#)
[Sales Drawings - SD052276-01](#)



A proud member of the Hubbell Family.