



YNA34R, 2-hole Aluminum Terminal

By Burndy
Catalog # [YNA34R](#)

HYLUG™, Aluminum Tube Compression Terminal, 2 Holes, 397.5 Kcmil ACSR, 397.5 - 477 Kcmil Al, 230 kV, 1.75" Spacing, Die Index: 719.



General

Connector Type	Terminal
Die Index	719
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016183
UPC 12 Digit	7818100161833

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	231 mm
Dimension - Length Overall inch	9.08 in
Dimension - Outside Diameter inch	1.3 in
Dimension - Pad Width inch	1.78 in
Dimension - Width fraction	1.78 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee-397.5 (30/7) Larkspur
Conductor - AL Str Size	397.5;400;450;477
Conductor - AL Str Size Range	397.5-477

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2880

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YNA-R15-2_LINEART_BW](#)
[Sales Drawings - sd062922-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YNA34R-SPEC-EN | REV 5/2024