



YNA34R45, Aluminum Terminal

By Burndy
Catalog # [YNA34R45](#)

Aluminum Compression Terminal 230 kV, 397.5 kcmil ACSR, 397.5-477 kcmil Alum., 4 Pad holes, 45 Deg.



General

Connector Type	Terminal
Die Index	719
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810372241
UPC 12 Digit	7818103722411

Dimensions

Dimension - B Length inch	4.21 in
Dimension - Outside Diameter inch	1.3 in
Dimension - Pad Width inch	1.78 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee-397.5 (30/7) Larkspur
Conductor - AL Str Size	397.5;400;450;477
Conductor - AL Str Size Range	397.5-477

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YNA34R45-SPEC-EN | REV 5/2024