



YNA36R45, Aluminum Terminal 45° Angle

By Burndy
Catalog # [YNA36R45](#)

Aluminum Compression Terminal 230 kV, 477 kcmil ASCR,
500-556.5 kcmil Alum., 45 Deg.



General

Connector Type	Terminal
Die Index	720
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283912
UPC 12 Digit	7818102839122

Dimensions

Dimension - B Length inch	4.47 in
Dimension - Height fraction	5-22/31 in
Dimension - Height inch	5.71 in
Dimension - L Length Overall mm	209 mm
Dimension - Length Overall inch	8.23 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	1.96 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

Product Assets

[3D Models - YNA36R45_MODEL-STEP](#)
[3D Models - YNA36R45_MODEL-IGES](#)
[3D Models - YNA36R45_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA36R45-SPEC-EN | REV 8/2023