



# YNA54RT15, ACSR - 15 Degree Compression Terminal

By Burndy  
Catalog # [YNA54RT15](#)



HYLUG™, Aluminum Compression terminal, 1431 Kcmil ACSR, 1590-1600 Kcmil Aluminum, 1534 Kcmil ACAR, Cable to Flat, 15 Deg, Terminal available with H/W.

## General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810096192
UPC 12 Digit	7818100961922

## Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.02 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

## Conductor Related

Conductor - ACAR Str Size	1534 KCMIL
Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover
Conductor - ACSR Str Size Range	1431 (54/19) Plover
Conductor - AL Str Size	1590 kcmil - 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil - 1600 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

## Product Assets

[3D Models - YNA54RT15\\_MODEL-STEP](#)  
[3D Models - YNA54RT15\\_MODEL-IGES](#)  
[3D Models - YNA54RT15\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..064930-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA54RT15-SPEC-EN | REV 8/2023