



YGHA312NTNNP Compression Grounding Lug, 350 kcmil Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated, No Oxide Inhibitor

By Burndy
Catalog # YGHA312NTNNP



Tin plated Heavy Duty Irreversible Compression Terminals without oxide inhibitor.

General

Connector Type	Terminal
Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810360606
UPC 12 Digit	7818103606066

Dimensions

Dimension - B Length fraction	1-9/50 in
Dimension - B Length inch	1.18 in
Dimension - D inch	3.03 in
Dimension - Height fraction	1-1/25 in
Dimension - Height inch	1.04 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	126 mm
Dimension - Length Overall inch	4.96 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.17 in
Dimension - Pad Width inch	1.62 in
Dimension - Z (inch)	0.66 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none">• UL467• UL 486A-486B• IEEE 837
Standards - Industry Standards Met	UL467;UL 486A-486B;IEEE 837
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	2220

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGHA312NTNNP-SPEC-EN | REV 5/2024