



YNA59R, Aluminum Terminal

By Burndy
Catalog # [YNA59R](#)

HYLUG™, Aluminum Compression terminal for ACSR, Aluminum, ACAR transmission lines, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Tube to flat, 4 Pad holes.



General

Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810460528
UPC 12 Digit	7818104605288

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	337 mm
Dimension - Length Overall inch	13.25 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.57 in
Dimension - Width fraction	3.57 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 kcmil;2300 kcmil
Conductor - AL Str Size Range	2250 kcmil;2300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd062922-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA59R-SPEC-EN | REV 8/2023