




YGIBS346132N Structural Steel Compression Grounding Connector

By Burndy
Catalog # YGIBS346132N



GROUNDLINK™ Connector for Structural Steel Angled or Parallel Beam; 2 Pad Holes; #2 AWG-500 kcmil; 1/2" Stud, I-Beam flange Thickness: .550" - .613".

General

Connector Type	Tap
I Beam Style	Standard Beam (Flange Angled)
Material	Copper
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Trade Name	GROUNDLINK™
Type	Taps
UPC	781810039335
UPC 12 Digit	7818100393355

Dimensions

Dimension - B Length fraction	6 in
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness Range inch	0.501;0.525;0.550;0.562
Dimension - I Beam Thickness inch	.550" - .613"
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1044

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGIBS283382N_LineArt](#)
[Sales Drawings - SD208416-04_B](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGIBS346132N-SPEC-EN | REV 5/2024