



# YNA59RT, ACSR - Compression Terminal

By Burndy  
Catalog # [YNA59RT](#)

Al Tube Compression Terminal, 4 Holes, 2156 -2167 Kcmil ACSR, 2250 - 2300 Kcmil Al, greater than 230 kV, 1.75" Spacing.



## Application

For ACAR And Stranded Aluminum Cable

## General

Connector Type	Terminal
Die Index	735
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YNA-RT
UPC	781810016466
UPC 12 Digit	7818100164666

## Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	344 mm
Dimension - Length Overall inch	13.54 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.57 in
Dimension - Width fraction	3.57 in

## Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 kcmil;2300 kcmil
Conductor - AL Str Size Range	2250 kcmil;2300 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..058036-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA59RT-SPEC-EN | REV 8/2023