

# Compression H-Tap

By Burndy  
Catalog # YH8C8CWC

Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 8 AWG-14 AWG Class B,C, 8 AWG-14 AWG Class I, DLO, Tap 1: 8 AWG-14 AWG Class B,C, 8 AWG-14 AWG Class I, DLO, kitted with black cover. See sale drawing for metric wire size accommodates



## Application

Wire Tap

## General

Color Code	Green
Connector Type	H-TAP W/BLK COVER
Die Index	11
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810000359
UPC 12 Digit	7818100003599

## Dimensions

Dimension - L Length Overall mm	15 mm
Dimension - Length Overall inch	0.60 in
Dimension - Strip Length inch	3/4
Dimension - Width inch	0.63 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	14;8
Conductor - Copper Flex G Tap	14;8
Conductor - Copper Flex H Tap	14;8
Conductor - Copper Flex I Run	8 AWG-14 AWG
Conductor - Copper Flex I Tap	14;8
Conductor - Copper Flex I Tap Range	8 AWG-14 AWG
Conductor - Copper Flex K Run	14;8
Conductor - Copper Flex K Tap	14;8
Conductor - Copper Flex M Run	14;8
Conductor - Copper Flex M Tap	14;8
Conductor - Copper Str Run	14;12;10;9;8
Conductor - Copper Str Run Range	8 AWG-14 AWG
Conductor - Copper Str Tap	14;12;10;9;8
Conductor - Copper Str Tap Range	8 AWG-14 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	3300

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD\\_206566-01](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YH8C8CWC-SPEC-EN | REV 5/2024