



YNA7M7T, Alumoweld - EHS Steel Compression Terminal

By Burndy
Catalog # [YNA7M7T](#)

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #7 Alumoweld, 7/16 Steel, 7 Str.



General

Connector Type	Terminal
Die Index	678;726
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810180525
UPC 12 Digit	7818101805255

Dimensions

Dimension - B Length inch	4.19 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	253 mm
Dimension - Length Overall inch	9.95 in
Dimension - Outside Diameter inch	1.00 in
Dimension - Pad Width inch	1.5 in

Conductor Related

Conductor - Galvanized Steel Str Size	7/16 (7) in
Conductor - Galvanized Steel Str Size Range	7/16 (7) in
Conductor Type	GAL Steel C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	3360

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd65301](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA7M7T-SPEC-EN | REV 8/2023