



# YNA7M8T, Alumoweld - EHS Steel Compression Terminal

By Burndy  
Catalog # [YNA7M8T](#)

Al Comp Static Wire Terminal, 2 Hole, 7 #8, 3 #5(Alumoweld),  
3/8" Steel, 7 Str, 7 #8, 3 #5(Alumoweld), 3/8" Steel, 7 Str.



## Application

For Alumoweld And EHS Steel

## General

Connector Type	Terminal
Construction Material - Main	Aluminum
Die Index	668;723
EU RoHS Indicator	Yes
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Type	YNA-M-T, Terminal
UPC	781810016138
UPC 12 Digit	7818100161388

## Dimensions

Dimension - B Length inch	3.49 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	249 mm
Dimension - Length Overall inch	9.81 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.5 in

## Conductor Related

Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in
Conductor Type	GAL Steel C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd65301](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA7M8T-SPEC-EN | REV 8/2023