



Heat Shrink Splice For 16 - 14 AWG

By Burndy
Catalog # [YHSS14](#)

Heat Shrink Splice For 16 - 14 AWG.



Application

For Use On Copper Conductor

General

| | |
|-------------------|----------------------|
| Connector Type | Seamless Butt Splice |
| EU RoHS Indicator | Yes |
| Insulation | Y |
| Insulation Type | Heat Shrink |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | HYDENT |
| Trade Name | HYDENT™ |
| Type | YHS, Heat Shrink |
| UPC | 781810476901 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 1/4 in |
| Dimension - B Length inch | 0.25 in |
| Dimension - L Length Overall mm | 38 mm |
| Dimension - Length Overall inch | 1.50 in |
| Dimension - Strip Length inch | 5/16 |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - Copper Solid Size | 16 AWG;15 AWG;14 AWG |
| Conductor - Copper Solid Size Range | 16 AWG-14 AWG |
| Conductor - Copper Str Size | 16 AWG;14 AWG |
| Conductor - Copper Str Size Range | 16 AWG - 14 AWG |
| Conductor Size | 16 - 14 AWG |
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 100 |
| Packaging Type | Bag |

Product Assets

[3D Models - YHSS14_MODEL-IGES](#)
[3D Models - YHSS14_MODEL-STEP](#)
[3D Models - YHSS14_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094203](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YHSS14-SPEC-EN | REV 8/2023