



Uninsulated Reducing Splice For 6 AWG and 8 AWG

By Burndy
Catalog # [YRV6CV8CL](#)



Uninsulated Reducing Splice For 6 AWG and 8 AWG.

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

General

Connector Type	Reducer
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810035917

Dimensions

Dimension - A Outside Diameter inch	0.3 in
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - B Outside Diameter inch	0.26 in
Dimension - Length BB inch	0.53 in
Dimension - Length Overall inch	1.18 in
Length	1.18 in

Conductor Related

Conductor - Copper Str Size	6
Conductor - Copper Str Size B	8
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[3D Models - YRV6CV8CL_MODEL-PDF](#)
[3D Models - YRV6CV8CL_MODEL-STEP](#)
[3D Models - YRV6CV8CL_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094202](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YRV6CV8CL-SPEC-EN | REV 8/2023