

YRV8CV10L, Uninsulated Reducing Splice For 8 AWG and 12 - 10 AWG

By Burndy
Catalog # [YRV8CV10L](#)

Cu Reducer Butt Splice, W/InspWindow, Barrel X:8 Barrel Y:10-12, 1.15" L, Tin Plated.



Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

General

Catalog Number	YRV8CV10L
Connector Type	Reducer
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810026380

Dimensions

Dimension - A Outside Diameter inch	0.27 in
Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - B Outside Diameter inch	0.21 in
Dimension - Length BB inch	0.53 in
Dimension - Length Overall inch	1.15 in
Length	1.15 in

Conductor Related

Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Str Size	8
Conductor - Copper Str Size B	10
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

- [3D Models - YRV8CV10L_MODEL-IGES](#)
- [3D Models - YRV8CV10L_MODEL-PDF](#)
- [3D Models - YRV8CV10L_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50094202](#)