

YNA32RT, 2-hole Aluminum Terminal

By Burndy
Catalog # YNA32RT



HYLUG™, Aluminum Tube Compression Terminal operates at 345 Kv, 300-336.4 Kcmil ACSR, 336.4-350 Kcmil Al, 395.1-395.5 Kcmil ACAR.

General

Catalog Number	YNA32RT
Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Number of Holes	2
Trade Name	HYLUG™
UPC	781810514825
UPC 12 Digit	7818105148255

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	232 mm
Dimension - Length Overall inch	9.14 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in
Dimension - Width fraction	1.68 in

Conductor Related

Conductor - ACAR Str Size	395.1;395.2
Conductor - ACAR Str Size Range	395.1;395.2
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350
Conductor - AL Str Size Range	336.4-350

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..058036-01](#)
- [Specifications - YNA32RT](#)