

YS28AT, Aluminum - Compression Splice

By Burndy
Catalog # [YS28AT](#)



Aluminum Compression Splice, 4/0 AWG, 5.05" Splice Length, Long Barrel, Tapered End, Tin Plated.

General

Catalog Number	YS28AT
Color Code	White
Connector Type	Splice
Die Index	298
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001394
UPC 14 Digit GTIN	00781810001394

Dimensions

Dimension - B Length inch	2.16 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.05 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Pad Width inch	2.42 in
Dimension - Strip Length inch	2 3/4

Conductor Related

Conductor - AL Str Size	4/0 AWG
-------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	12000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YS-AT_LineArt](#)
[Sales Drawings - SC..025626-01](#)
[Specifications - YS28AT](#)