



# YNA32RT15, 2-hole Aluminum Terminal 15° angle

By Burndy  
Catalog # [YNA32RT15](#)

HYLUG™, Aluminum Tube Compression Terminal operates at 345 Kv, 300-336.4 Kcmil ACSR, 336.4-350 Kcmil Al, 395.1-395.5 Kcmil ACAR, 15 Deg.



## General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Number of Holes	2
Trade Name	HYLUG™
UPC	781810514832
UPC 12 Digit	7818105148322

## Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.04 in
Dimension - Length Side A inch	9.04 in
Dimension - Length Side B inch	9.14 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in
Dimension - Width fraction	1.68 in
Physical Attribute - Tongue Angle	15 Degree

## Conductor Related

Conductor - ACAR Str Size Range	395.1;395.2
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil
Conductor - AL Str Size Range	336.4 (26/7) Linnet kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size Range	336.4;350
Conductor - AL Str Size Range	336.4-350

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..058036-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA32RT15-SPEC-EN | REV 8/2023