



YSA33R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # YSA33R2N



HYLUG™ Disconnectable Terminal, Barrel Partially filled with PENETROX™ oxide inhibitor, Accommodates: 397.5 KCMIL- 477 kcmil ASCR; 397 - 400 kcmil Aluminum conductors.

General

Connector Type	Terminal
Die Index	317
Material	Aluminum
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	3
Physical Attribute - Number of Holes	2
Prefilled Oxide Inhibitor	Y
UPC	781810262122

Dimensions

Dimension - B Length fraction	3-3/50 in
Dimension - B Length inch	3.06 in
Dimension - D inch	3.25 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	196 mm
Dimension - Length Overall inch	7.71 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.9 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee
Conductor - AL Str Size	397.5 KCMIL- 400 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd051201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSA33R2N-SPEC-EN | REV 8/2023