



YNA32RT15H, 2-hole Aluminum Terminal 15° angle

By Burndy
Catalog # [YNA32RT15H](#)

HYLUG™, Aluminum Tube Compression Terminal operates at 345 Kv, 300-336.4 Kcmil ACSR, 336.4-350 Kcmil Al, 395.1-395.5 Kcmil ACAR, Cable to flat, Terminal available with H/W, 15 Deg.



General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Number of Holes	2
Trade Name	HYLUG™
UPC	781810514849
UPC 12 Digit	7818105148499

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.04 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in
Dimension - Width fraction	1.68 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACAR Str Size Range	395.1;395.2
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size Range	336.4;350

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1440

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..058036-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA32RT15H-SPEC-EN | REV 8/2023