



Heat Shrink Splice For 22 - 18 AWG

By Burndy
Catalog # [YSE18HHS](#)



Heat Shrink Splice For 22 - 18 AWG.

Application

For Splicing Aircraft And Commercial Flexible Cables

General

Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YSE-H, Heat Shrink
UPC	781810525494

Dimensions

Dimension - Inside Diameter inch	0.17 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Strip Length inch	9/32 in

Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[3D Models - YSE18HHS_MODEL-PDF](#)
[3D Models - YSE18HHS_MODEL-STEP](#)
[3D Models - YSE18HHS_MODEL-IGES](#)
[Sales Drawings - 50094195](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSE18HHS-SPEC-EN | REV 8/2023