



YNA39R15, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA39R15](#)



HYLUG™, Aluminum Compression terminal, 556.5 Kcmil ACSR, 600-650 Kcmil Aluminum, 634.9-653.1 Kcmil ACAR, 250 Kv Max., 10.09 IN L, 15 Deg, Pad coated with oxide retardant.

General

Connector Type	Terminal
Die Index	722
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810180228
UPC 12 Digit	7818101802288

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.09 in
Dimension - Length Side A inch	10.09 in
Dimension - Length Side B inch	9.84 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.08 in
Dimension - Width fraction	2.08 in

Conductor Related

Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil
Conductor - AL Str Size	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	15
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YNA-R15-2_LINEART_BW](#)
[Sales Drawings - SD..064927-01](#)



A proud member of the Hubbell Family.