



Uninsulated Parallel Splice For 42,613 - 66,832 cmils

By Burndy
Catalog # [YSM2C](#)



Uninsulated Parallel Splice For 42,613 - 66,832 cmils.

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

General

Color Code	Brown
Connector Type	Parallel Splice
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805763
UPC 12 Digit	7818108057633

Dimensions

Dimension - Length Overall inch	0.62
Dimension - Outside Diameter inch	0.47
Dimension - Strip Length inch	11/16

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	42,613 - 66,832 cmils
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	99999

Product Assets

- [3D Models - YSM2C_MODEL-PDF](#)
- [3D Models - YSM2C_MODEL-IGES](#)
- [3D Models - YSM2C_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50094200](#)



A proud member of the Hubbell Family.