



YSU2W4W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # [YSU2W4W](#)



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Orange (Side A), Blue (Color Code).

General

Catalog Number	YSU2W4W
Color Code - Side A	Orange
Color Code - Side B	Blue
Die Index	243;BG or 5/8
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated, Center Stop
UPC	781810142080
UPC 12 Digit	7818101420800

Dimensions

Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2 in
Dimension - Outside Diameter inch	0.65 in

Conductor Related

Conductor - ACSR Str Size A	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - AL Str Size A	3 AWG, 4 AWG
Conductor - AL Str Size A Range	3 AWG- 4 AWG
Conductor - AL Str Size B	5 AWG, 6 AWG
Conductor - AL Str Size B Range	5 AWG-6 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size A	3 AWG, 4 AWG
Conductor - Copper Str Size A Range	3 AWG-4 AWG
Conductor - Copper Str Size B	5 AWG, 6 AWG
Conductor - Copper Str Size B Range	5 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29600

Product Assets

- [3D Models - YSU2W4W_MODEL-STEP](#)
- [3D Models - YSU2W4W_MODEL-IGES](#)
- [3D Models - YSU2W4W_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_YSU_LineArt](#)
- [Sales Drawings - sd052025-04](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSU2W4W-SPEC-EN | REV 6/2024