



YNA52RT45, Aluminum Terminal, 45° Angle

By Burndy
Catalog # [YNA52RT45](#)

Aluminum Compression terminal, 1113-1351.5 kcmil, 45 Deg,
345kV.



General

Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Pad Orientation	45 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810057759
UPC 12 Digit	7818100577599

Dimensions

Dimension - B Length inch	6.36 in
Dimension - L Length Overall mm	251 mm
Dimension - Length Overall inch	9.9 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACAR Str Size	1300 (61)
Conductor - ACAR Str Size Range	1300 (61)
Conductor - ACSR Str Size	1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Size Range	1113 (54/19) Finch-1272 (54/19) Pheasant
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[3D Models - YNA52RT45_MODEL-IGES](#)
[3D Models - YNA52RT45_MODEL-STEP](#)
[3D Models - YNA52RT45_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA52RT45-SPEC-EN | REV 8/2023