



YNA585RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA585RT](#)

HYLUG™, Al Tube Compression Terminal, operates 345 Kv, 2032.5-2034.5 Kcmil ACSR, Cable to flat, Extra high voltage applications.



General

Connector Type	Terminal
Die Index	735
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810221907
UPC 12 Digit	7818102219077

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	350 mm
Dimension - Length Overall inch	13.79 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.5 in
Dimension - Width fraction	3.50 in

Conductor Related

Conductor - ACSR Str Size	2032.1;2034.5
Conductor - ACSR Str Size Range	2032.1-2034.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	125
Pallet Quantity	360

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..058036-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA585RT-SPEC-EN | REV 8/2023