



YNA58RT90, Aluminum Terminal, 90° Angle

By Burndy
Catalog # [YNA58RT90](#)

Aluminum Compression terminal, 1780 kcmil, 90 Deg, 345 kV.



General

Connector Type	Terminal
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	90 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810283981
UPC 12 Digit	7818102839811

Dimensions

Dimension - B Length inch	7.53 in
Dimension - L Length Overall mm	234 mm
Dimension - Length Overall inch	9.2 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.75 in

Conductor Related

Conductor - ACSR Str Size	1780 (54/19) kcmil
Conductor - ACSR Str Size Range	1780 (54/19) kcmil
Conductor - AL Str Size	2000 kcmil
Conductor - AL Str Size Range	2000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..070287-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA58RT90-SPEC-EN | REV 8/2023