



YTW52RT521REKHT, Full Tension ACSS EHV Deadend Kit with Hardware

By Burndy
Catalog # [YTW52RT521REKHT](#)



Full Tension, ACSS EHV Deadend Kits, Hardware TMH9, 1192.5 (45/7) kcmil-1351.5 (45/7) kcmil, YTW52RT521REKHTNT Aluminum Dead End Assy., BYNA52RT15HHT Terminal.

Application

For 250 Deg C. rated ACSS transmission lines, Corona free operation up to 230 KV

General

Connector Type	Deadend
Physical Attribute - Number of Holes	4
Prefilled Oxide Inhibitor	N
UPC	781810222041
UPC 12 Digit	7818102220411

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size inch	1.25 in
Dimension - Length Overall inch	35.55 in
Dimension - Pad Width inch	4.00 in
Dimension - Width inch	1.00 in

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	1192.5 (45/7) kcmil;1192.5 (48/7) kcmil;1192.5 (54/19) kcmil;1272 (42/7) kcmil;1272 (45/7) kcmil;1272 (48/7) kcmil;1272 (54/19) kcmil;1351.5 (42/7) kcmil;1351.5 (45/7) kcmil
Conductor - ACSS Str Size Range	1192.5 (45/7) kcmil-1351.5 (45/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - 10085264](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTW52RT521REKHT-SPEC-EN | REV 8/2023