



## **AYP1/0, Compression Pin Adapter, 1/0 AWG, .29" Pin Dia, AL9CU**

By Burndy  
Catalog # [AYP1/0](#)

Aluminum Compression Pin Adapter, 1/0 AWG, 0.29" Plug Dia,  
0.84" Plug Length, Al/Cu Rated, Tin Plated.



## Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

## General

Application	
Catalog Number	AYP1/0
Color Code	Tan
Connector Type	INLINE PIN
Die Index	296
EU RoHS Indicator	Yes
Finish Type	Plaqué étain
Insulation	Y
Insulation Type	EPDM Rubber
Material	ALUMINUM
Physical Attribute - Number of	1
Crimps Required	
Pin Type	Solid
Plated	Y
Plating Type	Tin
Sub Brand	HYPLUG
Temperature Rating	194
Terminal Type	Pin
Trade Name	HYPLUG™
Type	
UPC	781810737583
UPC 12 Digit	7818107375833

## Dimensions

Dimension - A Outside Diameter inch	0.60 in
Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - B Outside Diameter inch	0.29 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.01 in
Dimension - P inch	0.84 in
Dimension - Strip Length inch Equivalent Pin Size	1-1/16 in 2 AWG

## Electrical Ratings

Voltage - Maximum Voltage Rating	35000 V 35 kV
----------------------------------	------------------

## Conductor Related

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper DLO Size	1 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG
Conductor - Copper Str Compact Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Pallet Quantity	11600

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50103891](#)



A Hubbell brand