



YNA594RT15, Aluminum Terminal, 4-hole, 15° Angle

By Burndy
Catalog # [YNA594RT15](#)

HYLUG™, Al Tube Compression Terminal, 15 Deg Bent, 4 Holes,
2300 Kcmil ACSR, 2500 Kcmil Al, 2267-2500 Kcmil ACAR,
1.75" Spacing.



General

Connector Type	Terminal
Die Index	740
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016435
UPC 12 Digit	7818100164355

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	343 mm
Dimension - Length Overall inch	13.5 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Pad Width inch	3.7 in
Dimension - Width fraction	3.70 in

Conductor Related

Conductor - ACAR Str Size	2267 KCML - 2500 KCMIL
Conductor - ACAR Str Size Range	2267 KCML - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YNA-RT15-2_LINEART_BW](#)
[Sales Drawings - SD..064930-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YNA594RT15-SPEC-EN | REV 5/2024