



# YNA7M10TH, Alumoweld - EHS Steel Compression Terminal

By Burndy  
Catalog # [YNA7M10TH](#)

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #10, 3 #7 Alumoweld, 5/16 Steel, 7 Str., H/W Kit is available.



## General

Connector Type	Terminal
Die Index	676;721
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810180518
UPC 12 Digit	7818101805188

## Dimensions

Dimension - B Length inch	2.68 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.5 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Pad Width inch	1.5 in

## Conductor Related

Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor Type	GAL Steel C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd65301](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA7M10TH-SPEC-EN | REV 8/2023