

YRV2CV6CL, Uninsulated Reducing Splice For 2 AWG and 6 AWG

By Burndy
Catalog # [YRV2CV6CL](#)



Uninsulated Reducing Splice For 2 AWG and 6 AWG.

Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

General

Catalog Number	YRV2CV6CL
Connector Type	Reducer
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810026366
UPC 14 Digit GTIN	00781810026366

Dimensions

Dimension - A Outside Diameter inch	0.46 in
Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.63 in
Dimension - B Outside Diameter inch	0.31 in
Dimension - Length BB inch	0.62 in
Dimension - Length Overall inch	1.60 in

Length 1.6 in

Conductor Related

Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Str Size	2
Conductor - Copper Str Size B	6
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	76800

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094202](#)
[Specifications - YRV2CV6CL](#)