



BA10EL6, Vinyl Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [BA10EL6](#)

Polyvinylchloride Insulated Locking Fork Compression Terminal;
Stud: #6.



Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

General

Catalog Number	BA10EL6
Connector Type	Locking Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLUG™
UPC	781810026885
UPC 12 Digit	7818100268855

Dimensions

Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Length Overall inch	1.05 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.26 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094176](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BA10EL6-SPEC-EN | REV 6/2024