

BA14E10M, Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [BA14E10M](#)

Vinyl Insulated Ring Terminal; Accommodates: #16 - #14 AWG;
Stud: #10; 600 V Max; 105 Degree Max.



Features

- Vinyl Ring Terminal banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

General

Catalog Number	BA14E10M
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810028964
UPC 12 Digit	7818100289644

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.85 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.26 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50093722](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-BA14E10M-SPEC-EN | REV 6/2024