


Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # YSE14HN



Nylon Splice For 16 - 14 AWG.

Application

For Heavy Duty Application Requirements

General

Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	YSE-HN
UPC	781810803875
UPC 12 Digit	7818108038755

Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Length Overall inch	1.23 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.23 in
Dimension - P inch	0.19 in
Dimension - Pad Width inch	0.15 in
Dimension - Strip Length inch	7/32 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[3D Models - YSE14HN_MODEL-IGES](#)
[3D Models - YSE14HN_MODEL-STEP](#)
[3D Models - YSE14HN_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094191](#)