


Nylon Splice For 22 - 18 AWG

By Burndy
Catalog # YSE18HBOX



Nylon Splice For 22 - 18 AWG.

Application

For Splicing Aircraft And Commercial Flexible Cables

General

Color Code	Red
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	YSE-H
UPC	781810566602
UPC 12 Digit	7818105666022

Dimensions

Cable Insulation Diameter Maximum	0.115 in
Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.22 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	9/32 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	20;18
Conductor - Copper Solid Size Range	20-18
Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Size	20;18
Conductor - Copper Str Size Range	20-18
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094194](#)

