



# Uninsulated Parallel Splice For 81,807 - 104,110 cmils

By Burndy  
Catalog # [YSM25](#)



Uninsulated Parallel Splice For 81,807 - 104,110 cmils.

## Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

## General

Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805831
UPC 12 Digit	7818108058311

## Dimensions

Dimension - Length Overall inch	0.69 in
Dimension - Outside Diameter inch	0.57 in
Dimension - Strip Length inch	3/4

## Conductor Related

Conductor - Copper Str Size	1 AWG;1/0
Conductor - Copper Str Size Range	1 AWG-1/0
Conductor Size	81,807 - 104,110 cmils
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	99999

## Product Assets

- [3D Models - YSM25\\_MODEL-STEP](#)
- [3D Models - YSM25\\_MODEL-PDF](#)
- [3D Models - YSM25\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50094200](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YSM25-SPEC-EN | REV 8/2023