



FD675D8, Substation - Copper Stud Connector

By Burndy
Catalog # [FD675D8](#)

Cast Cu Alloy Substation Stud Connector, Bolted, Stud to Pad, 1-3/4" -12 Stud, 230 kV, Silicon Bronze H/W, 1450 Amp.



Application

Substation

General

Catalog Number	FD675D8
Connector Type	Stud Connector
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Pad Configuration	4x4 - 4 holes
Plated	N
Plating Type	Unplated
Sub Brand	STUD CONNECTOR
Type	Studs
UPC	781810003282
UPC 12 Digit	7818100032822

Dimensions

Dimension - B Length fraction	2-9/50 in
Dimension - B Length inch	2.18 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.00 in
Dimension - L Length Overall mm	188 mm
Dimension - Length Overall inch	7.39 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-3/4 in
Dimension - Pin Diameter inch	1.750 in
Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

Electrical Ratings

Amperage Rating 1450 A

Conductor Related

Conductor - Connection Stud to Pad
Combination

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[3D Models - FD675D8_MODEL-PDF](#)
[3D Models - FD675D8_MODEL-IGES](#)
[3D Models - FD675D8_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section L - Bolted Substation](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_FD_LineArt](#)
[Sales Drawings - SD079583](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-FD675D8-SPEC-EN | REV 6/2024