



# Uninsulated Parallel Splice For 6,088 - 16,864 cmils

By Burndy  
Catalog # [YSM8C](#)



Uninsulated Parallel Splice For 6,088 - 16,864 cmils.

## Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

## General

Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805794
UPC 12 Digit	7818108057944

## Dimensions

Dimension - Length Overall inch	0.41 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Strip Length inch	1/2

## Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	12 AWG-8 AWG
Conductor Size	6,088 - 16,864 cmils
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200
Minimum Pack Quantity	200

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094200](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YSM8C-SPEC-EN | REV 8/2023