



## GAR1534, Ground Clamp, Cable to Rod or Pipe, 300-500 kcmil, #9-#10 Rebar, 1-1/8"-1-1/4" Rod, 1" Pipe

By Burndy  
Catalog # [GAR1534](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil, #9 - #10 Rebar, 1-1/8" to 1-1/4" Rod, 1" Pipe, Bright Dipped

### Features

- Wire to Rebar
- Fence Post Grounding Connector
- Wire to Pipe
- One-wrench installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for US and Canadian Markets
- Select connectors qualified to IEEE-837-2014

### General

Catalog Number	GAR1534
Installation Torque	480 Lb in
Recommended Run in-lb	
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
U Bolt Type	311
UPC	781810233009
UPC 14 Digit GTIN	00781810233009

### Dimensions

Dimension - B Length inch	2.19 in
Dimension - Height fraction	4-1/2 in
Dimension - Height inch	4.50 in
Dimension - Height mm	114.3 mm
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - Copper Solid Size	300 Kcmil
-------------------------------	-----------

Conductor - Copper Str Size	500 Kcmil
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Copper Tube Std Size Range	1 IPS IPS
Conductor - Pipe or Round Tube Size Range	1 in
Conductor - Rebar Size	9 ;10
Conductor - Rebar Size Range	9 -10
Conductor - Rod Size	1.120-1.31 in
Conductor - Rod Size Range	1 1/8 in-1 1/4 in
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li><li>• CU Tube Std-Size</li><li>• Rod-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Product Assets

[3D Models - GAR1534\\_MODEL-IGES](#)

[3D Models - GAR1534\\_MODEL-STEP](#)

[3D Models - GAR1534\\_MODEL-PDF](#)

[Catalogs - Burndy Grounding Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_GAR\\_Lineart](#)  
[Sales Drawings - SD..015789-01](#)  
[Sell Sheets - Type GAR, Parallel, 90° Connection to Rod/Pipe](#)

[Specifications - GAR1534 Specification Sheet English](#)  
[Specifications - BURNDY\\_GAR1534\\_Specsheet](#)  
[Specifications - GAR1534 Specification Sheet French](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
BRDY\_CA-GAR1534-SPEC-EN | REV 4/2025