



# YTW56RT590REK, Single Pad EHV Full Tension Deadend for ACSR

By Burndy  
Catalog # [YTW56RT590REK](#)

Single Pad, EHV Full Tension Deadend for ACSR Conductor.



\*Representative Image

## General

Connector Type	Deadend
Die Index	729
Material - Clevis	Steel
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	NEMA
Physical Attribute - Pad Orientation	15 Degree Angle
UPC	781810489055
UPC 12 Digit	7818104890555

## Dimensions

Dimension - B Length inch	2.69 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	813 mm
Dimension - Length Overall inch	31.99 in
Dimension - Pad Width inch	4.00 in

## Conductor Related

Conductor - ACSR Str Size	1590 (54/19) Falcon kcmil
---------------------------	---------------------------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50014613](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YTW56RT590REK-SPEC-EN | REV 8/2023