



Z34NR, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z34NR](#)



Socket And Nut Assembly, 500 kcmil, 5/8-18, 3-11/16 in L, Tin-Plated.

Features

- Socket and Nut Assembly designed for use with Burndy MOLE

Application

Designed for use with Burndy mole

General

Catalog Number	Z34NR
Connector Type	Nut
EU RoHS Indicator	Yes
Installation Torque	450 lb-in
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	MOLE
Type	Z-NR
UPC	781810821220
UPC 14 Digit GTIN	00781810821220

Dimensions

Dimension - B Length fraction	17/32 in
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	3.69
Weight	1.2 lb

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2784

Product Assets

- [3D Models - Z34NR_MODEL-PDF](#)
- [3D Models - Z34NR_MODEL-STEP](#)
- [3D Models - Z34NR_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ZNR_Lineart](#)
- [Sales Drawings - 50032378](#)
- [Specifications - Z34NR](#)