



HYTOOL™ Hand-Operated Crimper, Polymer Handles, D3 groove

By Burndy
Catalog # [MD76](#)

Hand-Operated HYTOOL™, Installs full range of connectors #14 - 4/0, 4.5 ton Crimp force, Weight: 7 LB, Snub-nose, permanent D3 groove only.



Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD76
Crimp Force Capacity	4.5 ton
Die Type	W and X Die
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimper
UPC	781810010921
UPC 12 Digit	7818100109211

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges

Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_082_OT2F_MD7_lineart2](#)
[Sales Drawings - se207642-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-MD76-SPEC-EN | REV 6/2024