



Full Cycle Ratchet Crimper, #22-10 AWG Nylon Insulated Terminals and Splices

By Burndy
Catalog # [MR18](#)

Full Cycle Ratchet Crimper, #22-10 AWG Nylon Insulated Terminals and Splices.



Application

Crimping

General

Application - For Use On	Nylon Insulated Terminals and Splices
Catalog Number	MR18
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810011201
UPC 12 Digit	7818100112011

Dimensions

Dimensions	8.88 in x 6.00 in x 2.50 in
Height	2.5 in
Length	8.88 in
Weight	1.1 lb
Width	6 in

Conductor Related

Crimping Ranges #22 - #10 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity 20
Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Installation Manuals - MR15 MR18, MR20 Operating Manual](#)
[Product Cross Section Image\(s\) - BUR_082_OTXF_MR15_MR18_MR20_lineart](#)
[Sales Drawings - 10113613](#)



A proud member of the Hubbell Family.