



Full Cycle Ratchet Crimper, #12-6 AWG INSULUG™

By Burndy
Catalog # [MR410M](#)

Full Cycle Ratchet Crimper, For use on #12-6 AWG INSULUG™.



Application

Crimping

General

Application - For Use On	Uninsulated Terminals and Splices
Die Type	Permanent Die Grooves
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810772065
UPC 12 Digit	7818107720655

Dimensions

Dimensions	11.75 in x 8.91 in x 1.00 in
Height	1 in
Length	11.75 in
Width	8.91 in

Conductor Related

Crimping Ranges #12 - #6 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_MR410M_LineArt](#)
[Sales Drawings - sd028976-01](#)



A proud member of the Hubbell Family.